



Not for use in wet weather

For indoor and outdoor installations

Fully insulated, massive switching stick head

Deep access into the installation

For use as operating rod for insulating protective

shutters in accordance with DIN VDE 0682 Teil 552

With plug-in coupling for extending the handle

SCS 123 STK 2000

| | |
|---|--|
| Nominal voltage U_N | 123 kV |
| Total length l_G | 2000 mm |
| Insertion depth l_o | 200 mm |
| Insulating tube | Glass-fibre reinforced polyester tube, Ø30 mm, grey |
| Switching pin | St, overall PVC sheathed, fixed |
| End fitting | Non-slip plastic cap / plug-in coupling for handle extension |
| Temperature range | -25° C ... +55° C |

Ordering information

| | |
|---------------------|------------------|
| Type | SCS 123 STK 2000 |
| Part No. | 763 180 |
| Packing unit | 1 pc |

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.