



Also for use in wet weather

For indoor and outdoor installations

Attachable switching stick head allows for use as switching stick

Supporting head for T pin shaft

Also for use as earthing stick

ISN 36 SQ 1500	
Nominal voltage U_N	36 kV
Maximum load on the operating head*)	17 kg
Total length l_G	1528 mm
Isolating distance	525 mm
Handle length l_H	500 mm
Insertion depth	500 mm
Insulating tube	Glass-fibre reinforced polyester tube, Ø30 mm, yellow
End fitting	Non-slip plastic cap / plug-in coupling for extending the handle
Ordering information	
Type	ISN 36 SQ 1500
Part No.	766 216
Packing unit	1 pc

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.